


# Product data sheet

Specifications



## Ultimate Screwless flat plate - switched socket - 2P - 2 gangs - piano black

GU3420DBBK

 **Discontinued on:** Dec 17, 2020

 **Discontinued**

### Main

Aesthetic Name	Screwless flat plate
Product Or Component Type	Switched socket
Rated Current	13 A at 230 V AC 50 Hz
Fixing Mode	By screws M3.5 x 30 mm
Colour Tint	Piano black

### Complementary

Device Presentation	Complete product
Outlet Poles Configuration	2P
Outlet Standard Description	3 pins
Outlet Standard	British
Actuator	Rocker
Number Of Gangs	2 gangs
Earth Circuit	Standard earth
Pilot Light	Without neon indicator
Device Mounting	Wall mounted
Connections - Terminals	Screw terminal
Material	Polycarbonate
Quantity Per Set	Set of 1
Height	88 mm
Width	148 mm
Depth	30 mm

### Environment

Ip Degree Of Protection	IP20
Standards	BS 1363

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>