

Product data sheet

Specifications



Ultimate Metal clad - switched socket - 13 A - 230 V - 2 gangs - silver grey

GU3633GMCS

⚠ Discontinued on: Mar 24, 2005

⚠ Discontinued

Main

Range Of Product	Ultimate
Aesthetic Name	Metal clad
Product Or Component Type	Switched socket
Device Presentation	Complete product
Outlet Standard	British
Colour Tint	Silver grey matt
Socket Additional Information	Outboard socket T-shaped earth pin
Earth Circuit	Clean earth
Quantity Per Set	Set of 1

Complementary

Switch Function	2-pole
Rated Current	13 A at 230 V AC 50 Hz
Actuator	Rocker
Number Of Gangs	2 gangs
Pilot Light	without neon indicator
Fixing Mode	By screws
Connections - Terminals	Screw terminals
Material	Powder coated steel
Type Of Installation	Indoor
Depth	42 mm
Width	139 mm
Height	79 mm
Net Weight	0.446 kg

Environment

Standards	BS 1363
Ip Degree Of Protection	IP20

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months