

# Product data sheet

Specifications



Switched fused connection, Ultimate  
Screwless flat plate, switch, screw  
terminals, stainless steel

GU5413WSS

## Main

|                           |                           |
|---------------------------|---------------------------|
| Aesthetic Name            | Screwless flat plate      |
| Product Or Component Type | Switched fused connection |
| Switch Function           | Switch                    |
| Colour Tint               | Steel<br>White            |

## Complementary

|                         |                        |
|-------------------------|------------------------|
| Pilot Light             | without neon indicator |
| Number Of Gangs         | 1 gang                 |
| Material                | Steel                  |
| Mounting Support        | Wall mounted           |
| Fixing Mode             | By screws              |
| Rated Current           | 13 A at 230 V AC       |
| Connections - Terminals | Screw terminals        |
| Quantity Per Set        | Set of 1               |
| Height                  | 88 mm                  |
| Width                   | 88 mm                  |
| Depth                   | 26 mm                  |

## Environment

|                         |         |
|-------------------------|---------|
| Ip Degree Of Protection | IP20    |
| Standards               | BS 1363 |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 4.000 cm  |
| Package 1 Width              | 9.500 cm  |
| Package 1 Length             | 9.600 cm  |
| Package 1 Weight             | 240.000 g |
| Unit Type Of Package 2       | CAR       |
| Number Of Units In Package 2 | 100       |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |            |
|------------------------------|------------|
| Package 2 Height             | 21.500 cm  |
| Package 2 Width              | 42.500 cm  |
| Package 2 Length             | 50.000 cm  |
| Package 2 Weight             | 24.740 kg  |
| Unit Type Of Package 3       | PAM        |
| Number Of Units In Package 3 | 1600       |
| Package 3 Height             | 102.500 cm |
| Package 3 Width              | 120.000 cm |
| Package 3 Length             | 100.000 cm |
| Package 3 Weight             | 415.840 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|  |  |
|--|--|
|  Mercury Free               |  |
|  Rohs Exemption Information | <a href="#">Yes</a>                    |
| Reach Regulation   | <a href="#">REACH Declaration</a>      |
| Eu Rohs Directive  | Compliant with Exemptions              |
| China Rohs Regulation  | <a href="#">China RoHS declaration</a> |