

# Product data sheet

Specifications



Switched fused connection, Ultimate  
Screwless flat plate, switch, screw  
terminals, IP20, chrome

GU5414WPC

## Main

Aesthetic Name	Screwless flat plate
Product Or Component Type	Switched fused connection
Switch Function	Switch
Colour Tint	White Chrome

## Complementary

Pilot Light	Red neon indicator
Number Of Gangs	1 gang
Material	Steel
Mounting Support	Wall mounted
Fixing Mode	By screws
Rated Current	13 A at 230 V AC
Connections - Terminals	Screw terminals
Quantity Per Set	Set of 1
Height	88 mm
Width	88 mm
Depth	26 mm

## Environment

Ip Degree Of Protection	IP20
Standards	BS 1363

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	4.200 cm
Package 1 Length	10.300 cm
Package 1 Weight	200.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	21.000 cm
Package 2 Width	44.000 cm
Package 2 Length	53.000 cm
Package 2 Weight	25.145 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	115.000 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	402.320 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Under investigation
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information