

Product data sheet

Specifications



Data socket, Ultimate Screwless flat plate, RJ45, screw terminal, black nickel

GU7471BBN

Main

Range	Ultimate
Aesthetic Name	Screwless flat plate
Product Or Component Type	Data socket
Data Socket Type	RJ45
Quantity Per Set	Set of 1
Colour Tint	Black nickel, polished Black

Complementary

Number Of Gangs	1 gang
Communication Network Type	RJ45
Connections - Terminals	Screw terminal
Type Of Installation	Indoor
Material	Steel
Fixing Mode	By screws
Height	88 mm
Width	88 mm
Depth	35 mm

Environment

Ip Degree Of Protection	IP20
Standards	BS EN 41003

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.600 cm
Package 1 Width	9.500 cm
Package 1 Length	9.600 cm
Package 1 Weight	209.600 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	21.000 cm
Package 2 Width	30.000 cm
Package 2 Length	49.000 cm
Package 2 Weight	10.926 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	100.500 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	369.626 kg

Contractual warranty

Warranty	18 months
----------	-----------