

Product data sheet

Specifications



Ultimate Screwless flat plate - shaver socket - white metal/white

GU7490WPW

Main

Range Of Product	Ultimate
Aesthetic Name	Screwless flat plate
Product Or Component Type	Shaver socket
Input Voltage	230 V AC 50 Hz
Colour Tint	Painted white polished White

Complementary

Material	Steel
Fixing Mode	By screws M3.5 x 30 mm
Device Mounting	Flush
Connections - Terminals	Screw terminals
Quantity Per Set	Set of 1
Height	148 mm
Width	88 mm
Depth	47 mm

Environment

Standards	BS EN 61558-2-5
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	10.1 cm
Package 1 Length	16 cm
Package 1 Weight	865 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	17.5 cm
Package 2 Width	30 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	43 cm
Package 2 Weight	17.68 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	800
Package 3 Height	104 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	727.2 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration