

# Product data sheet

Specifications



## Ultimate Slim line - euro modular plate - 2 modules - grey

GU8060GY

### Main

Range	Ultimate
Device Application	Mounting
Aesthetic Name	Slimline
Product Or Component Type	Front plate
Range Compatibility	Ultimate front plate
Mounting Mode	Flush-mounted
Colour Tint	Grey matt

### Complementary

Installation Direction	Horizontal/vertical
Number Of Modules	2 modules
Number Of Gangs	1 gang
Fixing Mode	By screws
Material	Plastic
Quantity Per Set	Set of 10
Width	86 mm
Height	86 mm

### Environment

Ip Degree Of Protection	IP20
-------------------------	------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.7 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	37 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9 cm
Package 2 Width	9 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	10 cm
Package 2 Weight	408 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	200
Package 3 Height	20.5 cm
Package 3 Width	21.7 cm
Package 3 Length	47 cm
Package 3 Weight	8.51 kg

# Sustainability


**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Rohs Exemption Information	Yes
<hr/>	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
<hr/>	
China Rohs Regulation	<a href="#">China RoHS declaration</a>
<hr/>	
Circularity Profile	No need of specific recycling operations
<hr/>	