

Product data sheet

Specifications



Ultimate - screwless KNX flat plate - 1 gang - pearl nickel

GU8434PN

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Ultimate
Device Application	Mounting
Aesthetic Name	Screwless flat plate
Product Or Component Type	Front plate
Range Compatibility	Ultimate front plate
Mounting Mode	Flush-mounted
Colour Tint	Pearl nickel matt

Complementary

Installation Direction	Horizontal/vertical
Number Of Gangs	1 gang
Fixing Mode	By screws
Material	Stainless steel
Width	86 mm
Height	86 mm

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	9.7 cm
Package 1 Length	9.7 cm
Package 1 Weight	131 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21 cm
Package 2 Width	43 cm
Package 2 Length	50 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	13.82 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	100.5 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	241.1 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration