

Product data sheet

Specifications



Blind cover, Ultimate Euro, 2 gangs,
polished chrome

GU8520PC

Main

Range	Ultimate
Aesthetic Name	Low profile
Product Or Component Type	Cover plate
Colour Tint	Chrome

Complementary

Range Compatibility	Ultimate Ultimate Low Profile
Device Mounting	Wall mounted
Fixing Mode	By screws
Number Of Gangs	2 gangs
Number Of Modules	1 module
Surface Finish	Varnished
Material	Steel
Height	88 mm
Width	148 mm
Depth	15 mm
Net Weight	0.144 kg

Environment

Standards	BS 5733
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.100 cm
Package 1 Width	9.600 cm
Package 1 Length	15.500 cm
Package 1 Weight	185.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	17.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	43.800 cm
Package 2 Length	51.000 cm
Package 2 Weight	10.060 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1000
Package 3 Height	104.000 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	221.200 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration