

# Product data sheet

Specifications



## Ultimate - euro modular low profile plate - 2 gangs - brushed chrome

GU8560BC

### Main

Aesthetic Name	Low profile
Product Or Component Type	Front plate
Mounting Mode	Flush-mounted
Colour Tint	Chrome brushed finish

### Complementary

Number Of Gangs	2 gangs
Fixing Mode	By screws
Quantity Per Set	Set of 1
Width	88 mm
Height	88 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.400 cm
Package 1 Width	10.000 cm
Package 1 Length	11.000 cm
Package 1 Weight	121.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	6.000 cm
Package 2 Width	11.000 cm
Package 2 Length	11.000 cm
Package 2 Weight	635.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	24.500 cm
Package 3 Width	24.500 cm
Package 3 Length	32.500 cm
Package 3 Weight	13.010 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>