

# Product data sheet

Specifications



## Switch module, Ultimate Grid system, 2-way, snap-on, IP20, black

GUG20DPMB

### Main

Range Of Product	Ultimate
Range	Ultimate
Device Application	Control
Aesthetic Name	Grid system
Product Or Component Type	Switch module
Switch Function	2-way
Rated Current	20 AX at 230 V AC

### Complementary

Connections - Terminals	Snap-on
Material	Thermoplastic
Quantity Per Set	Set of 1
Number Of Gangs	1 gang

### Environment

Standards	BS EN 60669-1
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	2.4 cm
Package 1 Length	5.9 cm
Package 1 Weight	30.9 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	6.5 cm
Package 2 Width	6.5 cm
Package 2 Length	10.1 cm
Package 2 Weight	206.9 g
Unit Type Of Package 3	CAR

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	600
Package 3 Height	15.5 cm
Package 3 Width	52 cm
Package 3 Length	69 cm
Package 3 Weight	21.591 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability


**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Rohs Exemption Information	Yes
<hr/>	
Reach Regulation	<a href="#">REACH Declaration</a>
<hr/>	
Eu Rohs Directive	Compliant with Exemptions
<hr/>	
China Rohs Regulation	<a href="#">China RoHS declaration</a>
<hr/>	