

Product data sheet

Specifications



Ultimate - indicator module - orange neon indicator lamp - 250 V

GUGINDWO

Main

Range Of Product	Ultimate
Product Or Component Type	Indicator module
Colour Tint	Insert: white
Quantity Per Set	1

Complementary

Pilot Light	Orange neon indicator
Bulb Type	Neon
Fixing Mode	Snap-fitted
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Material	Nylon PC (polycarbonate)
Height	59 mm
Width	25 mm
Depth	23 mm

Environment

Standards	BS 5733
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	6.6 cm
Package 1 Length	8.5 cm
Package 1 Weight	23 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	6.6 cm
Package 2 Width	6.5 cm
Package 2 Length	8.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	165 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	600
Package 3 Height	15.5 cm
Package 3 Width	45.5 cm
Package 3 Length	67 cm
Package 3 Weight	17.244 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration