

Product data sheet

Specifications



empty enclosure, for TeSys GV2ME, IP41

GV2MC01

Main

Range	TeSys
Product or component type	Enclosure
Device short name	GV2MC
Accessory / separate part category	Mounting accessory
Product compatibility	GV2ME
Enclosure type	Surface mounting

Complementary

Auxiliary mounting location	Left Right
Height	147 mm
Width	93 mm
Depth	84 mm

Environment

IP degree of protection	IP41
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10 cm
Package 1 Width	10 cm
Package 1 Length	15.2 cm
Package 1 Weight	263 g
Unit Type of Package 2	S04
Number of Units in Package 2	27
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm

Package 2 Weight	8.258 kg
Unit Type of Package 3	P06
Number of Units in Package 3	108
Package 3 Height	80 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	41.912 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)