

Product data sheet

Specifications



Galaxy VM Level 2 Seismic Kit for Narrow Modular Battery Cabinet

GVML2MBCN-KIT

Overview

Presentation	Kit includes parts and fasteners to achieve Seismic level 2 certification
Lead Time	Usually in Stock

Physical

Height	10.6 cm
Width	37 cm
Depth	81.7 cm
Net Weight	17 kg

Conformance

Product Certifications	C-Tick RCM
Standards	EN/IEC 62040-1 EN/IEC 62040-2 EN/IEC 62040-3 UL 1778

Environmental

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	-25...65 °C
Storage Altitude	0.00...14999.82 m
Storage Relative Humidity	0...95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	20.3 cm
Package 1 Width	86.4 cm
Package 1 Length	40.6 cm
Package 1 Weight	18.14 kg

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Energy Efficient Take-back Transparency

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)