

# Product data sheet

Specifications



## Galaxy VX 625kVA 480V Remote Maintenance Bypass Cabinet

GVXMBCR625KG

### Overview

Presentation	Maintenance bypass cabinet which can be installed remotely and isolates the UPS during service operations.
Lead Time	Special Order - Call for Quoted Lead Times

### Physical

Colour	Black
Height	197 cm
Width	80 cm
Depth	90 cm
Net Weight	280 kg

### Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	215 cm
Package 1 Width	106 cm
Package 1 Length	99 cm
Package 1 Weight	300 kg

### Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability


**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Rohs Exemption Information [Yes](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information