

Product data sheet

Specifications



Thorsman Analogue Multimeter Cat III

IMT23213

⚠ Discontinued on: Dec 19, 2023

⚠ Discontinued

Main

Range	Thorsman
Product Or Component Type	Analog multimeter
Supply	battery 1.5 V

Complementary

Type Of Setting	Manual
Function Available	Handsfree operations
Protection Type	Fuse
Type Of Measurement	Resistance: x10 Ohm/x1 kOhm Voltage DC: 12/60/120/300 V Voltage AC: 12/60/300 V Current DC: 0.6/12/600 mA
Measurement Category	Category III 300 V
Relative Humidity	0...85 %
User Language	French Polish Hungarian
Height	140 mm
Width	75 mm
Depth	50 mm
Product Weight	275 g without battery

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	15.000 cm
Package 1 Length	26.000 cm
Package 1 Weight	358.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.000 cm
Package 2 Weight	4.725 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	96
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	49.800 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration