

Product data sheet

Specifications



Thorsman 18W LED - worklight Contour plug Nordics

IMT33095

⚠ Discontinued on: Sep 6, 2021

⚠ Discontinued

Main

Range	Thorsman
Product Name	Thorsman 18 LED
Product Or Component Type	Work lamp
Light Source	42 x SMD LED 5630 18 W

Complementary

Type Of Installation	Outdoor Indoor
[Ue] Rated Operational Voltage	100...240 V
Network Type	AC
Network Frequency	50/60 Hz
Plug Pole Configuration	2P
Plug Standard	Contour
Luminous Flux	1500 lm
Bulb Lifespan	50000 h
Colour Rendering Index	R _a =80
Beam Angle	100 °
Cable Insulation Material	Neoprene
Material	TPE (thermoplastic elastomer) ABS (acrylonitrile butadiene-styrene)
Electrical Connection	Power cord H05RN-F2x1.0 2 m
Electrical Insulation Class	Class II
Height	200 mm
Width	200 mm
Depth	80 mm
Net Weight	0.99 kg
Targeted Country	Norway Denmark Finland Sweden Holland

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Dustproof Splashproof
Ip Degree Of Protection	IP54
Ik Degree Of Protection	IK07
Quality Labels	CE
Ambient Air Temperature For Operation	-25...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21 cm
Package 1 Width	25.6 cm
Package 1 Length	11.5 cm
Package 1 Weight	1.188 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations