

# Product data sheet

Specifications



Mureva U56 - j box - 10 grommets  
87x87x39mm - 5-pole screw term -  
polarwhite

IMT34077

## Main

Range Of Product	Mureva
Product Name	Mureva BOX
Device Short Name	U56
Product Or Component Type	Junction box
Device Application	Cable installation
Colour Tint	White (RAL 9003)
Quantity Per Set	Set of 2

## Complementary

Device Mounting	Surface
Fixing Mode	By screw: body housing
Base Dimension	75 x 45 x 65 mm
Cable Entry	Grommets
Cable Entry Number	10 diameter: 14 mm
Material	ABS (acrylonitrile butadiene-styrene)
Height	87 mm
Width	87 mm
Depth	39 mm

## Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP55
Standards	EN 60670-1
Product Certifications	NEMKO SEMKO FIMKO DEMKO

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.7 cm
Package 1 Weight	88.793 g
Unit Type Of Package 2	SFP
Number Of Units In Package 2	5
Package 2 Height	8.7 cm
Package 2 Width	8.7 cm
Package 2 Length	19 cm
Package 2 Weight	429.2 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	150
Package 3 Height	45.5 cm
Package 3 Width	29.5 cm
Package 3 Length	40 cm
Package 3 Weight	13.319 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations