

Product data sheet

Specifications



Mureva K60 - j box w/o grommets 60x60x30mm - without terminal - polarwhite

IMT34092

Main

Range Of Product	Mureva
Product Name	Mureva BOX
Device Short Name	K60
Product Or Component Type	Junction box
Device Application	Cable installation
Colour Tint	White (RAL 9003)
Quantity Per Set	Set of 2

Complementary

Device Mounting	Surface
Fixing Mode	By screw: body housing
Base Dimension	76 x 45 x 65 mm
Material	PA (polyamide) 6/PP (polypropylene)
Height	60 mm
Width	60 mm
Depth	30 mm

Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP20
Standards	EN 60670-1
Product Certifications	FIMKO NEMKO DEMKO SEMKO

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.900 cm
Package 1 Width	6.100 cm
Package 1 Length	6.000 cm
Package 1 Weight	30.000 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	CAR
Number Of Units In Package 2	350
Package 2 Height	29.400 cm
Package 2 Width	39.600 cm
Package 2 Length	45.000 cm
Package 2 Weight	11.300 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations