

# Product data sheet

Specifications



Mureva U56 - j box - 10 grom  
87x87x39mm on tray plate - w/o  
termi - polarwhite

IMT34096

## Main

|                           |                    |
|---------------------------|--------------------|
| Range Of Product          | Mureva             |
| Product Name              | Mureva BOX         |
| Device Short Name         | U56                |
| Product Or Component Type | Junction box       |
| Device Application        | Cable installation |
| Colour Tint               | White (RAL 9003)   |
| Quantity Per Set          | Set of 2           |

## Complementary

|                    |                                       |
|--------------------|---------------------------------------|
| Device Mounting    | Surface                               |
| Fixing Mode        | By screw: body housing                |
| Base Dimension     | 80 x 45 x 65 mm                       |
| Cable Entry        | Grommets                              |
| Cable Entry Number | 10 diameter: 14 mm                    |
| Material           | ABS (acrylonitrile butadiene-styrene) |
| Height             | 120 mm                                |
| Width              | 180 mm                                |
| Depth              | 38 mm                                 |

## Environment

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature For Operation | -25...60 °C                      |
| Ip Degree Of Protection               | IP55                             |
| Standards                             | EN 60670-1                       |
| Product Certifications                | DEMKO<br>FIMKO<br>NEMKO<br>SEMKO |

## Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 5.8 cm |
| Package 1 Width              | 12 cm  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |           |
|------------------------------|-----------|
| Package 1 Length             | 18 cm     |
| Package 1 Weight             | 309.325 g |
| Unit Type Of Package 2       | BB1       |
| Number Of Units In Package 2 | 5         |
| Package 2 Height             | 18.4 cm   |
| Package 2 Width              | 13.3 cm   |
| Package 2 Length             | 26.8 cm   |
| Package 2 Weight             | 1.44 kg   |
| Unit Type Of Package 3       | S04       |
| Number Of Units In Package 3 | 40        |
| Package 3 Height             | 30 cm     |
| Package 3 Width              | 40 cm     |
| Package 3 Length             | 60 cm     |
| Package 3 Weight             | 12.257 kg |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |