

# Product data sheet

Specifications



## Apparatus box, Multifix Air, 1 gang, 67x40 mm, green

IMT35001

### Main

Range Of Product	Multifix
Product Name	Multifix Air
Product Or Component Type	Apparatus box
Device Application	For airtight installation

### Complementary

Function Available	Anti-rotation system
Number Of Gangs	1 gang
Fixing Mode	By supplied screw
Material	PP/TPE
Mechanical Robustness	Airtight Fire resistance
Colour Tint	Green (NCS S 2070-G80Y)
Cable Entry	4 knock-outs
Distance Between Centers	71 mm
Drill Diameter/Depth	67 mm 40 mm
Distance Between Supports	60 mm
Height	71 mm
Width	71 mm
Depth	39 mm

### Environment

Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP40
Fire Resistance	850 °C
Standards	EN 60670-1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.800 cm
Package 1 Width	7.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	7.000 cm
Package 1 Weight	22.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	21.000 cm
Package 2 Width	25.000 cm
Package 2 Length	28.800 cm
Package 2 Weight	1.300 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	2400
Package 3 Height	105.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	72.632 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations