

Product data sheet

Specifications



Multifix Air, apparatus box, 1 gang, 67x50 mm

IMT35002

⚠ Discontinued on: May 13, 2016

⚠ Discontinued

Main

Range Of Product	Multifix
Product Name	Multifix Air
Product Or Component Type	Apparatus box
Device Application	For airtight installation
Device Presentation	Without cover

Complementary

Function Available	Anti-rotation system
Number Of Gangs	1 gang
Fixing Mode	By supplied screw
Material	PP/TPE
Mechanical Robustness	Fire resistance Airtight
Colour Tint	Green (NCS S 2070-G80Y)
Cable Entry	4 knock-outs
Distance Between Centers	71 mm
Drill Diameter/Depth	67 mm 50 mm
Distance Between Supports	60 mm
Height	71 mm
Width	71 mm
Depth	49 mm

Environment

Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP20
Fire Resistance	850 °C
Standards	EN 60670-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4.9 cm
Package 1 Width	7.1 cm
Package 1 Length	7.1 cm
Package 1 Weight	0.025 kg

Contractual warranty

Warranty	18 months
----------	-----------