

# Product data sheet

Specifications



## Multifix Air, wall box kit, 1 gang, with surface cover

IMT35028

### Main

Range Of Product	Multifix
Product Name	Multifix Air
Product Or Component Type	Wall box kit
Device Application	For airtight installation
Device Presentation	With surface cover
Provided Equipment	Surface cover IPX4 DCL outlet

### Complementary

Function Available	Anti-rotation system
Number Of Gangs	1 gang
Fixing Mode	By supplied screw
Material	PP/TPE ABS (acrylonitrile butadiene-styrene) PC/ABS
Mechanical Robustness	Airtight Fire resistance
Colour Tint	Green (NCS S 2070-G80Y)
Cable Entry	4 knock-outs
Drill Diameter/Depth	67 mm 40 mm
Distance Between Supports	60 mm
Height	71 mm
Width	71 mm
Depth	39 mm

### Environment

Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP20
Fire Resistance	850 °C
Standards	EN 60670-1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4.000 cm
Package 1 Width	12.000 cm
Package 1 Length	12.000 cm
Package 1 Weight	49.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	11.900 cm
Package 2 Width	20.200 cm
Package 2 Length	33.300 cm
Package 2 Weight	611.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	50
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	3.850 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations