

# Product data sheet

Specifications



## Mureva – IP65 junc box – 14 membranes - 87x87 mm – w/o terminal - anthracite

IMT35336

### Main

Range Of Product	Mureva
Product Or Component Type	Junction box
Device Application	Cable installation
Colour Tint	Anthracite (RAL 7016)
Quantity Per Set	Set of 5

### Complementary

Device Mounting	Surface
Fixing Mode	By screws: body housing
Base Dimension	87 x 87 x 42 mm
Cable Entry	Grommets
Cable Entry Number	14 diameter: 19 mm
Material	PP (polypropylene)
Height	87 mm
Width	87 mm
Depth	42 mm
Net Weight	62 g

### Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP65
Glow Wire Temp	650 °C
Standards	EN 60670
Product Certifications	DEMKO FIMKO NEMKO SEMKO

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	8.700 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.700 cm
Package 1 Weight	61.400 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8.700 cm
Package 2 Width	8.700 cm
Package 2 Length	22.000 cm
Package 2 Weight	307.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	60
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.781 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations