

# Product data sheet

Specifications



## Mureva – IP65 junc box – 14 membranes - 87x87 mm – w/o term - anthracite

IMT35345

### Main

|                           |                       |
|---------------------------|-----------------------|
| Range Of Product          | Mureva                |
| Product Or Component Type | Junction box          |
| Device Application        | Cable installation    |
| Colour Tint               | Anthracite (RAL 7016) |

### Complementary

|                    |                         |
|--------------------|-------------------------|
| Device Mounting    | Surface                 |
| Fixing Mode        | By screws: body housing |
| Base Dimension     | 87 x 87 x 42 mm         |
| Cable Entry        | Grommets                |
| Cable Entry Number | 14 diameter: 19 mm      |
| Material           | PP (polypropylene)      |
| Height             | 87 mm                   |
| Width              | 87 mm                   |
| Depth              | 42 mm                   |
| Net Weight         | 62 g                    |

### Environment

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature For Operation | -25...60 °C                      |
| Ip Degree Of Protection               | IP65                             |
| Glow Wire Temp                        | 650 °C                           |
| Standards                             | EN 60670                         |
| Product Certifications                | DEMKO<br>FIMKO<br>NEMKO<br>SEMKO |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 4.5 cm |
| Package 1 Width              | 8.6 cm |
| Package 1 Length             | 8.6 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |          |
|------------------------------|----------|
| Package 1 Weight             | 65.0 g   |
| Unit Type Of Package 2       | S03      |
| Number Of Units In Package 2 | 60       |
| Package 2 Height             | 30.0 cm  |
| Package 2 Width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 4.318 kg |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |