

Product data sheet

Specifications



Thorsman TET - grommet - grey - ISO M32 - diameter 14 to 20

IMT36183

Main

Product Range	Thorsman TET
Product Type	Grommet
Colour	Grey
Quantity Per Package	Set of 50

Complementary

Material	EPDM
Iso Thread	M32
Cable Outer Diameter	14...20 mm
Drilling Diameter	32.4 mm
Height	30 mm
Width	48 mm
Length	48 mm

Environment

Ip-Class	IP67
----------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	3.8 cm
Package 1 Length	3.8 cm
Package 1 Weight	12.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	25.0 cm
Package 2 Width	16.0 cm
Package 2 Length	7.0 cm
Package 2 Weight	625.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	850

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	40.0 cm
Package 3 Width	32.0 cm
Package 3 Length	30.0 cm
Package 3 Weight	11.082 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)