

Product data sheet

Specifications



Thorsman TET - grommet - grey - ISO M40 - diameter 20 to 26

IMT36184

Main

Product Range	Thorsman TET
Product Type	Grommet
Colour	Grey
Quantity Per Package	Set of 25

Complementary

Material	EPDM
Iso Thread	M40
Cable Outer Diameter	20...26 mm
Drilling Diameter	40.7 mm
Height	30 mm
Width	60 mm
Length	60 mm

Environment

Ip-Class	IP67
----------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	5.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	27.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	25
Package 2 Height	6.0 cm
Package 2 Width	16.0 cm
Package 2 Length	26.0 cm
Package 2 Weight	688.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	400

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	30.0 cm
Package 3 Width	29.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	11.422 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations