

Product data sheet

Specifications



Multifix Eco - apparatus box - single - 4 flexible stubs - w/o cover - 10/27mm

IMT36192

⚠ Discontinued on: Dec 30, 2021

⚠ End-of-service on: Feb 2, 2022

⚠ Discontinued

Main

| | |
|---------------------------|---------------|
| Range Of Product | Multifix |
| Product Name | Multifix Eco |
| Device Short Name | VP-2 A |
| Product Or Component Type | Apparatus box |
| Device Application | Single board |
| Quantity Per Set | Set of 50 |

Complementary

| | |
|---------------------------|--|
| Device Mounting | Flush |
| Device Composition | Adjustable threaded screw ring Without cover Stub with locking tabs of stainless steel |
| Mounting Support | Board - thickness: 10...27 mm |
| Number Of Stubs | 4 flexible - diameter: 16 mm |
| Number Of Gangs | 1 gang |
| Colour Tint | Grey (NCS 3500) |
| Material | PEHD (polyethylene high density) (untreated) |
| Distance Between Supports | 60 mm |
| Diameter | 70 mm |
| Internal Depth | 55 mm |
| Length | 160 mm |
| Width | 57 mm |
| Depth | 71 mm |
| Net Weight | 0.078 kg |
| Cable Cross Section | 2.5 mm ² |
| Tube Diameter | 16 mm |
| Sealing | Without |
| Connections - Terminals | Snap-on |

Environment

| | |
|-----------|-------------|
| Standards | IEC 60670-1 |
|-----------|-------------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|-------------|
| Ambient Air Temperature For Operation | -25...90 °C |
| Ip Degree Of Protection | IP20 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.7 cm |
| Package 1 Width | 7.1 cm |
| Package 1 Length | 15.8 cm |
| Package 1 Weight | 62 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |