

Product data sheet

Specifications



Mureva U56 - junction box - 10 grommets - without terminal - russian label

IMT36349

! Discontinued

! Discontinued on: Oct 22, 2018

! End-of-service on: Dec 5, 2018

Main

Range Of Product	Mureva
Product Or Component Type	Junction box
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 5

Complementary

Device Mounting	Surface
Fixing Mode	By screws: cover
Base Dimension	87 x 87 x 39 mm
Cable Entry	Grommets
Cable Entry Number	10 diameter: 19 mm
Material	ABS (acrylonitrile butadiene-styrene): body and cover SEBS (styrene ethylene butylene styrene): grommet
Height	87 mm
Width	87 mm
Depth	39 mm
Net Weight	0.073 kg

Environment

Ambient Air Temperature For Operation	-25...40 °C
Ip Degree Of Protection	IP65
Glow Wire Temp	650 °C
Standards	EN 60670 CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	74.78 g
------------------	---------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)