

Product data sheet

Specifications



Thorsman - MMS-MF 7.5x50 - screw - hexagonal - set of 50

IMT38046

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Thorsman
Product Or Component Type	Screw
Device Short Name	MMS-MF
Device Application	Concrete and solid brick materials
Screw Type	Fully threaded
Provided Equipment	combined washer
Tool Type	cordless screwdriver 10 mm wrench
Quantity Per Set	Set of 50

Complementary

Drilling Diameter	6 mm
Screw Diameter	7.5 mm
Screw Length	50 mm
Shape Of Screw Head	Hexagonal
Material	Screw: steel electroplated
Atmospheric-Corrosivity Category	C4

Environment

Standards	CE
-----------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.75 cm
Package 1 Width	0.75 cm
Package 1 Length	5 cm
Package 1 Weight	7.1 g

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations