

Product data sheet

Specifications



Mureva lights, Floodlight 20W 4000K, IP44 IR Sensor 230V

IMT47216

Main

Range	Mureva
Range Of Product	Mureva lights
Product Or Component Type	Floodlight
Device Application	Ware-houses and parking garages Residential Media device support Public areas Secure lighting Stadiums and arenas

Complementary

Type Of Installation	Outdoor
Total System Power	20 W
Light Source	LED
[Ue] Rated Operational Voltage	230 V AC
Power Factor	0.7
Colour Rendering Index	R _a =80
Luminous Flux	2000 lm
Bulb Lifespan	50000 h
Colour Temperature	4000 K
Colour Tint	Black
Provided Equipment	Sensor
Electrical Insulation Class	Class F
Beam Angle	110 °
Shape	Rectangular
Height	163.4 mm
Width	181.4 mm
Depth	26.0 mm
Net Weight	570 g

Environment

Environmental Characteristic	Weatherproof
Ip Degree Of Protection	IP44
Ik Degree Of Protection	IK04

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-30...45 °C
---------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.2 cm
Package 1 Width	19.2 cm
Package 1 Length	19.2 cm
Package 1 Weight	630 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	10
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	7.003 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	68.024 kg

Contractual warranty

Warranty	3 years
----------	---------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

 Sustainable Packaging

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information