

# Product data sheet

Specifications



## Mureva lights, Floodlight 20W 6500K, IP44 IR Sensor 230V

IMT47217

### Main

Range	Mureva
Range Of Product	Mureva lights
Product Or Component Type	Floodlight
Device Application	Ware-houses and parking garages Residential Media device support Public areas Secure lighting Stadiums and arenas

### Complementary

Type Of Installation	Outdoor
Total System Power	20 W
Light Source	LED
[Ue] Rated Operational Voltage	230 V AC
Power Factor	0.7
Colour Rendering Index	R <sub>a</sub> =80
Luminous Flux	2000 lm
Bulb Lifespan	50000 h
Colour Temperature	6500 K
Colour Tint	Black
Provided Equipment	Sensor
Electrical Insulation Class	Class F
Beam Angle	110 °
Shape	Rectangular
Height	163.4 mm
Width	181.4 mm
Depth	26.0 mm
Net Weight	570 g

### Environment

Environmental Characteristic	Weatherproof
Ip Degree Of Protection	IP44
Ik Degree Of Protection	IK04

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-30...45 °C
---------------------------------------	-------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.2 cm
Package 1 Width	19.2 cm
Package 1 Length	19.2 cm
Package 1 Weight	630 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	10
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	7.003 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	68.024 kg

## Contractual warranty

Warranty	3 years
----------	---------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)





Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

 Sustainable Packaging

## Well-being performance

 Mercury Free

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>