

Product data sheet

Specifications



Thorsman, Worklight 30W, IP65 Contour Plug 230V

IMT47226

Main

Range	Thorsman
Range Of Product	Thorsman Worklights
Product Name	Worklight
Product Or Component Type	Lamp
Device Application	Mobile equipment Ware-houses and parking garages Hospital Residential Sports hall

Complementary

Type Of Installation	Outdoor
[Ue] Rated Operational Voltage	230 V
Network Type	AC
Operational Power In W	30 W
Plug Standard	Contour
Luminous Flux	3000 lm
Bulb Lifespan	50000 h
Colour Rendering Index	R _a =80
Colour Temperature	4000 K
Beam Angle	110 °
Power Factor	0.9
Height	254.5 mm
Width	231.0 mm
Depth	20.0 mm
Net Weight	1.1 kg

Environment

Environmental Characteristic	Water resistant Dust resistant UV resistant Impact resistant
Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK05
Ambient Air Temperature For Operation	-30...45 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	26 cm
Package 1 Width	26 cm
Package 1 Length	26 cm
Package 1 Weight	1.7 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	5
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	8.941 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	155.056 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)