

# Product data sheet

Specifications



## Mureva Flex GT HF - pliable GT conduit - diam. 20 - black - LSF0H - IP67

IMT49004

### Main

Range Of Product	Mureva Flex GT HF
Product Or Component Type	Pliable conduit
Function Available	GT-function
Mounting Location	Indoor
Nominal Cross Section	133 mm²
Diameter	Internal: 13 mm External: 20 mm
Colour Tint	Black (RAL 9005)
Length	50 m

### Complementary

Resistance To Compression	750 N
Material	PP (polypropylene)
Quantity Per Set	50 m
Ambient Air Temperature For Operation	-25...105 °C
Standards	IEC 61034 IEC 60754-2 IEC 60754-1 EN 50267-2-1 EN 50268 IEC 61386 EN 50267-2-2

### Environment

Ip Degree Of Protection	IP67 with coupling
Product Certifications	NF
Environmental Characteristic	Non-flame propagating

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	2 cm
Package 1 Length	21 cm
Package 1 Weight	69 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	45 cm
Package 2 Width	45 cm
Package 2 Length	21 cm
Package 2 Weight	3.464 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	2100
Package 3 Height	210 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	158 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations