

# Product data sheet

Specifications



## Stago - feeder trunking - 170 x 40 mm - steel - white - RAL 9010

INS16480212

⚠ Discontinued on: Sep 30, 2020

⚠ End-of-service on: Oct 26, 2020

⚠ Discontinued

### Main

Range Of Product	Stago
Product Or Component Type	Feeder trunking
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 1

### Complementary

Trunking Dimension	170 x 65 mm 120 x 65 mm 170A x 65 mm
Compartment Partitioning	1 compartment
Nominal Cross Section	6800 mm²
Material	Zinc coated sheet steel
Surface Finish	Powder coated
Length	1000 mm
Height	170 mm
Width	40 mm

### Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17 cm
Package 1 Width	4 cm
Package 1 Length	100 cm
Package 1 Weight	4.11 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



## Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

Circularity Profile	No need of specific recycling operations
---------------------	--