

# Product data sheet

Specifications



## OptiLine 50 - post - two-sided - natural

INS42510

⚠ Discontinued on: Jul 21, 2021

⚠ End-of-service on: Feb 2, 2022

⚠ Discontinued

### Main

|                           |                        |
|---------------------------|------------------------|
| Range                     | OptiLine               |
| Product Name              | OptiLine 50            |
| Product Type              | Post                   |
| Type Of Post              | Two-sided              |
| Configuration             | Complete product       |
| Colour Tint               | Natural                |
| Number Of Socket          | 12 x 16 A - side earth |
| Quantity Package 1 / Unit | Set of 1               |

### Complementary

|                               |                      |
|-------------------------------|----------------------|
| Pole/Post Surface Finish      | Anodized             |
| Front Opening Size            | 50 mm                |
| Number Of Data Socket Outlets | 4 x RJ45 Cat.6 S/FTP |
| Fixing Mode                   | By screws            |
| Product Material              | Aluminium            |
| Height                        | 600 mm               |
| Width                         | 156 mm               |

### Environment

|                         |             |
|-------------------------|-------------|
| Operating Temperature   | -25...60 °C |
| Ip Degree Of Protection | IP30        |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 60 cm   |
| Package 1 Width              | 15.6 cm |
| Package 1 Length             | 12.5 cm |
| Package 1 Weight             | 5.8 kg  |

### Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

|                          |   |
|--------------------------|---|
| <b>Eu Rohs Directive</b> | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
|--------------------------|---|

|                              |   |
|------------------------------|---|
| <b>China Rohs Regulation</b> | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
|------------------------------|---|

|                                 |   |
|---------------------------------|---|
| <b>Environmental Disclosure</b> | <a href="#">Product Environmental Profile</a> |
|---------------------------------|---|

|                            |  |
|----------------------------|--|
| <b>Circularity Profile</b> | No need of specific recycling operations |
|----------------------------|--|