


Product data sheet

Specifications



OptiLine 50 - post - four-sided - natural

INS42520

 **Discontinued on:** Nov 19, 2020

 **Discontinued**

Main

Range	OptiLine
Product Name	OptiLine 50
Product Type	Post
Type Of Post	Four-sided
Configuration	Complete product
Colour Tint	Anthracite (RAL 7043)
Number Of Socket	24 x 16 A - side earth
Quantity Package 1 / Unit	Set of 1
Cover Type	4 closed cover cover 50 mm in plastic untreated

Complementary

Pole/Post Surface Finish	Anodized
Front Opening Size	50 mm
Number Of Data Socket Outlets	8 x RJ45 Cat.6 S/FTP
Fixing Mode	By screws
Product Material	Aluminium
Height	600 mm
Width	200 mm
Adjustment	Fixed:
Useful Cross Section	13966 mm ²
Compartment Partitioning	1 compartment

Environment

Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP30

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18 cm
Package 1 Width	20 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	60 cm
Package 1 Weight	13 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations