

Product data sheet

Specifications



Stago - t-piece, riser - 170 x 72 mm - steel - white - RAL 1013

INS5553622

⚠ Discontinued on: Sep 26, 2017

⚠ End-of-service on: Oct 26, 2017

⚠ Discontinued

Main

Range Of Product	Stago
Product Or Component Type	T-piece
Provided Equipment	1 x cover
Colour Tint	White (RAL 1013)
Quantity Per Set	Set of 1

Complementary

Trunking Dimension	170 x 72 mm
Compartment Partitioning	1 compartment
Front Opening Size	80 mm
Nominal Cross Section	12240 mm²
Fixing Mode	By screws By brackets
Material	Zinc coated sheet steel
Surface Finish	Powder coated
Length	400 mm
Height	170 mm
Width	72 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17 cm
Package 1 Width	7.2 cm
Package 1 Length	40 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1744 g
------------------	--------