

Product data sheet

Specifications



Stago - internal corner - 165W x 52 mm - steel - white - RAL 9010

INS5554213

 **Discontinued on:** Mar 30, 2020

 **Discontinued**

Main

Range Of Product	Stago
Product Or Component Type	Internal corner
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 1

Complementary

Trunking Dimension	165W x 52 mm
Compartment Partitioning	1 compartment
Front Opening Size	80 mm
Nominal Cross Section	8580 mm ²
Fixing Mode	By screws By brackets
Material	Zinc coated sheet steel
Surface Finish	Powder coated
Length	200 mm
Height	165 mm
Width	52 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.5 cm
Package 1 Width	5.2 cm
Package 1 Length	20 cm
Package 1 Weight	1.026 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations