

Product data sheet

Specifications

Stago - front cover F80 - 1500 mm - steel - unpainted



INS5596005

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Stago
Product Or Component Type	Front cover
Quantity Per Set	3 m

Complementary

Trunking Dimension	170 x 65 mm 110 x 52 mm 233 x 72 mm 120 x 65 mm 110 x 72 mm 165W x 52 mm 130 x 72 mm 183 x 72 mm 170A x 65 mm 165V x 52 mm 170 x 72 mm
Front Opening Size	80 mm
Fixing Mode	Snap-fitted
Material	Zinc coated sheet steel
Surface Finish	Unpainted
Length	1500 mm
Height	80 mm
Width	12.7 mm
Compatibility Code	WGX-F80

Environment

Standards	EN 50085-1:2005
Ambient Air Temperature For Operation	-20...80 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	1.2 cm
Package 1 Length	100 cm
Package 1 Weight	1 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations