


Product data sheet

Specifications



OptiLine 50 - adaptor - GST 18i3 male - 10 pieces

INS60010

⚠ Discontinued on: Sep 30, 2022

⚠ Discontinued

Main

Range Of Product	OptiLine 50
Product Type	Adaptor
Colour	White
Quantity Package 1 / Unit	10 pieces

Complementary

Interface	GST 18i3 male / OSI interface (3 poles)
Product Material	PA (polyamide)
Length	55 mm
Height	16 mm
Width	37 mm

Environment

Operating Temperature	-5...40 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	3.7 cm
Package 1 Length	5.5 cm
Package 1 Weight	18.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	7.2 cm
Package 2 Width	8.2 cm
Package 2 Length	14.0 cm
Package 2 Weight	180.0 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	750

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	30.0 cm
Package 3 Width	40.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	14.465 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	No need of specific recycling operations
---------------------	--