

# Product data sheet

Specifications



## OptiLine 45 - joint cover piece - PC/ ABS - aluminium metallic

ISM10456

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

Range Of Product	OptiLine 45
Cabling Installation System	Trunking
Product Type	Joint cover piece
Colour	Aluminium metallic
Quantity Package 1 / Unit	Set of 1

### Complementary

Trunking Material	Aluminium
Trunking Dimension	165 x 55 mm
Fixing Mode	Snap-fitted
Product Material	PC/ABS painted
Length	100 mm
Height	170 mm
Width	57 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17 cm
Package 1 Width	5.7 cm
Package 1 Length	2.4 cm
Package 1 Weight	46 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BAG
Number Of Units In Package 2	60
Package 2 Height	30 cm
Package 2 Width	29.9 cm
Package 2 Length	39.8 cm
Package 2 Weight	3.121 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	480
Package 3 Height	45 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	36.968 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information      [Yes](#)

<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
--------------------------	---

<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	---

<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
---------------------------------	---

<b>Circularity Profile</b>	No need of specific recycling operations
----------------------------	--