

Product data sheet

Specifications



OptiLine 45 OptiLine 70 - stop end - PC/ABS - aluminium metallic

ISM10554

Main

Range Of Product	OptiLine 45 OptiLine 70
Cabling Installation System	Trunking
Product Type	Stop end
Colour	Aluminium metallic
Quantity Package 1 / Unit	Set of 2

Complementary

Trunking Material	Aluminium
Trunking Dimension	185 x 55 mm
Fixing Mode	Snap-fitted Screw
Product Material	PC/ABS painted
Length	21 mm
Height	189 mm
Width	56 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.900 cm
Package 1 Width	5.600 cm
Package 1 Length	2.100 cm
Package 1 Weight	55.000 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BAG
Number Of Units In Package 2	100
Package 2 Height	29.900 cm
Package 2 Width	30.000 cm
Package 2 Length	39.800 cm
Package 2 Weight	5.500 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	800
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	51048.000 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations