

Product data sheet

Specifications



OptiLine 45 - front cover - polar white

ISM10960P

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Cabling Installation System	Pole Post
Product Or Component Type	Front cover

Complementary

Type Of Pole	One-sided Two-sided
Type Of Post	Two-sided One-sided
Colour Tint	Polar white (RAL 9003)
Quantity Per Set	24 m
Trunking Material	Plastic
Trunking Dimension	75 x 55 mm 165 x 55 mm 140 x 55 mm 95 x 55 mm 185 x 55 mm
Pole/Post Surface Finish	Powder coated
Pole Fixing Mode	Free-standing Tension-mounted
Fixing Mode	Snap-fitted
Material	Aluminium
Length	2000 mm
Height	45 mm
Width	16 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	1.6 cm
Package 1 Length	200 cm
Package 1 Weight	327 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	24
Package 2 Height	5.7 cm
Package 2 Width	12.1 cm
Package 2 Length	203.3 cm
Package 2 Weight	8.251 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	960
Package 3 Height	36.8 cm
Package 3 Width	120.0 cm
Package 3 Length	210.0 cm
Package 3 Weight	355.04 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations