

Product data sheet

Specifications



Optiline - Mini trunking DCL branching piece - 15x35 - Polar white

ISM14791P

⚠ Discontinued on: Sep 30, 2022

⚠ Discontinued

Main

Range	OptiLine
Accessory / Separate Part Category	Mounting accessory
D_Range_Compatibility	OptiLine

Complementary

Trunking Material	Plastic
Colour Tint	Polar white (RAL 9003)
Trunking Dimension	15 x 35 mm
Fixing Mode	Snap-fitted
Material	PC/ABS
Quantity Per Package	Set of 10
Operating Temperature	-15...60 °C

Environment

Standards	73/23/EEC EN 50085-1:2005 EN 50085-2-1:2006
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	4 cm
Package 1 Length	7.8 cm
Package 1 Weight	12 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	150
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm

Package 2 Weight	2.953 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	1200
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	30.024 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

Eu Rohs Directive Not applicable, out of EU RoHS legal scope

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations
