

Product data sheet

Specifications



Thorsman - TML-E - joint cover piece - floor - white RAL 9010

ISM18007

⚠ Discontinued on: Feb 5, 2019

⚠ End-of-service on: Mar 29, 2019

⚠ Discontinued

Main

Range Of Product	Thorsman
Product Name	Thorsman TML-E
Product Or Component Type	Joint cover piece
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 5

Complementary

Trunking Material	Plastic
Fixing Mode	Snap-fitted
Material	ABS (acrylonitrile butadiene-styrene) untreated
Length	43 mm
Height	81 mm
Width	24 mm

Environment

Standards	EN 50085-1:1997/A1 EN 50085-1:1998
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP40

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.1 cm
Package 1 Width	4.3 cm
Package 1 Length	2.4 cm
Package 1 Weight	7 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)