

# Product data sheet

Specifications



## OptiLine 45 - pole - tension-mounted - two-sided - natural - 2700-3100 mm

ISM20106

### Main

Range	OptiLine
Product Name	OptiLine 45
Shape	Oval
Cabling Installation System	Pole
Product Type	Pole
Device Presentation	Empty
Type Of Pole	Two-sided
Pole/Post Surface Finish	Anodized
Pole Fixing Mode	Tension-mounted
Adjustment	Adjustable in height: 400 mm

### Complementary

Additional Information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front Opening Size	45 mm
Material	Aluminium anodized
Quantity Package 1 / Unit	Set of 1
Height	2700...3100 mm
Depth	90 mm
Width	116 mm
Cover Type	2 closed cover cover 45 mm in aluminium anodized
Useful Cross Section	696 mm²
Compartment Partitioning	2 compartments

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP30

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.0 cm
Package 1 Width	16.5 cm
Package 1 Length	315.0 cm
Package 1 Weight	8.8 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	28
Package 2 Height	66.0 cm
Package 2 Width	120.0 cm
Package 2 Length	400.0 cm
Package 2 Weight	266.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations