

Product data sheet

Specifications



OptiLine 45 - pole - tension-mounted - one-sided - natural - 3900-4300 mm

ISM20120

Main

Range	OptiLine
Product Name	OptiLine 45
Cabling Installation System	Pole
Product Type	Pole
Device Presentation	Empty
Type Of Pole	One-sided
Pole/Post Surface Finish	Anodized
Pole Fixing Mode	Tension-mounted
Socket Additional Information	Unearthed

Complementary

Additional Information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front Opening Size	45 mm
Material	Aluminium anodized
Quantity Package 1 / Unit	Set of 1
Height	3900...4300 mm
Depth	89 mm
Width	68 mm

Environment

Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP30

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.500 cm
Package 1 Width	16.000 cm
Package 1 Length	396.000 cm
Package 1 Weight	11.000 kg
Unit Type Of Package 2	PAL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	28
Package 2 Height	54.000 cm
Package 2 Width	120.000 cm
Package 2 Length	420.000 cm
Package 2 Weight	320.000 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations