

# Product data sheet

Specifications



## OptiLine 45 - Unica floor outlet box - 8 modules



ISM50538

### Main

Cabling installation system	Floor box
Product type	Unica floor outlet box
Type of floor	Raised floor In-cavity floor Screeded floor
Floor box shape	Rectangular
Colour	Grey (RAL 7011)
Quantity package 1 / unit	1 piece

### Complementary

Number of modules	8 modules
Product material	Steel PA6 PBT (polybutylene terephthalate)
Length	199 mm
Height	72 mm
Width	276 mm

### Environment

Standards	73/23/EEC 93/68/EEC IEC 61084-1:ed. 1, 1991 IEC 61084-2-2:2003
Operating temperature	-25...60 °C
IP degree of protection	IP20

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	21.5 cm
Package 1 Length	29.0 cm
Package 1 Weight	1.495 kg
Unit Type of Package 2	P12

<b>Number of Units in Package 2</b>	120
<b>Package 2 Height</b>	112.0 cm
<b>Package 2 Width</b>	80.0 cm
<b>Package 2 Length</b>	120.0 cm
<b>Package 2 Weight</b>	190.44 kg

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Recommended replacement(s)