

# Product data sheet

Specifications



## OptiLine 45 - Fuga floor outlet box - 6 modules

ISM51736

### Main

Cabling Installation System	Floor box
Product Type	Fuga floor outlet box
Type Of Floor	Screeded floor Raised floor In-cavity floor
Floor Box Shape	Rectangular
Quantity Package 1 / Unit	1 piece

### Complementary

Number Of Modules	6 modules
Product Material	Stainless steel ABS (acrylonitrile butadiene-styrene) PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene)
Length	199 mm
Height	82 mm
Width	276 mm

### Environment

Standards	73/23/EEC 93/68/EEC IEC 61084-1:ed. 1, 1991 IEC 61084-2-2:2003
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	19.9 cm
Package 1 Length	27.6 cm
Package 1 Weight	2.35 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations